

# tekmar® - Job Record

## tN2 Zone Expansion Module 324



**J324**

08/09

Control Name / Location \_\_\_\_\_ Connected to Zone Manager \_\_\_\_\_

Zone	1	2	3	4	Zone 4 Cooling & Fan		tN4 Expansion Connections	
Label					Cool (Rc - Y)	Fan (Rc - G)	Control Label	
Thermostat Model							Model	
Schedule Heat / Cool							Location	
Cool Group							Bus #	
Address								


**Dip Switch Settings**  
(circle / fill-in the correct setting)

**Zone Group Pump**

1	On	Off
2	On	Off
3	On	Off
4	On	Off

**Zone Group Pump Delay**

1	On	Off
2	On	Off
3	On	Off
4	On	Off



Zone Power	1	2	3	4
Label				
Make				
Model				
Design Flow				
Valve VA	+	+	+	=
Pump Amp	+	+	+	=

Transformer VA must exceed \_\_\_\_\_

Max 12 A

Zone Group Pump		Line Voltage Input 115 V (ac)
Label		
Make		
Model		
Amps	(Max. 5 A)	Combined Total Amps =
Design Flow		
Design Head		Max. 11.7 A

**Notes:**

Blank job records can be downloaded from the tekmar website at <http://www.tekmarcontrols.com>



tekmar Control Systems Ltd., Canada  
tekmar Control Systems, Inc., U.S.A.  
**Head Office: 5100 Silver Star Road**  
**Vernon, B.C. Canada V1B 3K4**  
**(250) 545-7749 Fax. (250) 545-0650**  
**Web Site: [www.tekmarcontrols.com](http://www.tekmarcontrols.com)**