

tekmar® - Job Record


Zone Manager 335



J335
08/09

Control Name / Location _____ Connected to Module _____

Zone Group A	External tN4 Input / Output	Pump A Input 24 V (ac)	Zone	A1	A2	A3	A4	A5	A6	Total Tstat + Left Side Module VA	
Control Label			Label								
Model			Thermostat Model								
Location			Schedule Heat / Cool								
Bus #			Cool Group								
			Address								
VA from left side module =			+	VA	+	+	+	+	+	=	



Dip Switch Settings
(circle / fill-in the correct setting)

Zone Group Pump A

A1	On	Off
A2	On	Off
A3	On	Off
A4	On	Off
A5	On	Off
A6	On	Off

Zone Group Pump A Delay

A1	On	Off
A2	On	Off
A3	On	Off
A4	On	Off
A5	On	Off
A6	On	Off

Total Tstat + Left Side Module + Zone Valve VA

Max. 50 VA
24 V (ac)
See W335 to add extra VA

Line Voltage Input 115 V (ac)	Zone Group Pump A	Zone Valves	A1	A2	A3	A4	A5	A6	Total Zone Valve VA	
Combined Total Amps =	Label	Label								
Max. 11.5 A	Make	Make								
	Model	Model								
	Amps (Max. 5 A)	VA	+	+	+	+	+	+		=
	Design Flow	Design Flow								
	Design Head	Notes								

Notes:

Blank job records can be downloaded from the tekmar website at <http://www.tekmarcontrols.com>



tekmar Control Systems Ltd., Canada
tekmar Control Systems, Inc., U.S.A.
Head Office: 5100 Silver Star Road
Vernon, B.C. Canada V1B 3K4
(250) 545-7749 Fax. (250) 545-0650
Web Site: www.tekmarcontrols.com

