

tekmar® Submittal

Universal Sensor 078



Accessories


C078

01/11

Replaces: New

Job _____ Designer _____ Contact _____

The Universal Sensor 078 is a temperature sensor. It is useful for a wide range of applications, from sensing boiler supply temperature to slab temperature. The 15 ft. rigid cable makes this sensor useful for feeding into existing conduit or other challenging locations.



Specifications

Universal Sensor 078	
Literature	D078
Packaged weight	0.5 lb. (230 g), brass sleeve, 15' (4.6 m) 18 AWG, 220°F (105°C) PVC jacketed 300 V wire
Dimensions	3/8" OD x 3/4" (9.5 OD x 19 mm)
Approvals	CSA C US
Operating range	-60 to 221°F (-51 to 105°C)
Sensor	NTC thermistor, 10 kΩ @ 77°F (25°C ±0.2°C) β=3892
Warranty	Limited 3 Year (See D078 for full warranty)

Features

- 10K thermistor
- Stiff jacketed cable for easy wiring in conduit

Temperature vs. Resistance

Temperature		Resistance	Temperature		Resistance	Temperature		Resistance	Temperature		Resistance
°F	°C	Ω	°F	°C	Ω	°F	°C	Ω	°F	°C	Ω
-40°	-40°	336,479	68°	20°	12,493	176°	80°	1,255	284°	140°	235
-31°	-35°	242,681	77°	25°	10,000	185°	85°	1,070	293°	145°	208
-22°	-30°	176,974	86°	30°	8,057	194°	90°	915	302°	150°	186
-13°	-25°	130,421	95°	35°	6,531	203°	95°	786	311°	155°	166
-4°	-20°	97,081	104°	40°	5,326	212°	100°	678	320°	160°	148
5°	-15°	72,957	113°	45°	4,368	221°	105°	587	329°	165°	133
14°	-10°	55,329	122°	50°	3,602	230°	110°	510	338°	170°	119
23°	-5°	42,327	131°	55°	2,986	239°	115°	445	347°	175°	107
32°	0°	32,650	140°	60°	2,488	248°	120°	389	356°	180°	97
41°	5°	25,392	149°	65°	2,083	257°	125°	341	365°	185°	87
50°	10°	19,901	158°	70°	1,752	266°	130°	301	374°	190°	79
59°	15°	15,712	167°	75°	1,480	275°	135°	265	383°	195°	72

SPECIAL REQUIREMENTS

N / A



tekmar Control Systems Ltd., Canada, tekmar Control Systems, Inc., U.S.A. **Head Office: 5100 Silver Star Road, Vernon, B.C. Canada V1B 3K4, 250-545-7749, Fax. 250-545-0650 Web Site: www.tekmarcontrols.com**

