Job Name	Contractor
Job Location	Approval
Engineer	Contractor's P.O. No
Approval	Representative



Deringer[™] 50X Low Head Loss Reduced Pressure Detector Assembly

Sizes: 6"

The Deringer[™] 50X Reduced Pressure Detector Assembly (RPDA-II) prevents non-health hazard pollutants and hazardous contaminants entering a potable water supply system when backpressure and/or backsiphonage conditions occur. Used primarily on fire sprinkler systems when monitoring of unauthorized water use is required.

Features

- Oversized checks for extreme performance
- Poppet action first check for more reliable relief valve closure
- Stainless steel braided wire sensing line
- Stem includes tamper switch groove
- Inline serviceable gate valves
- Stainless steel housing
- Tamper-resistant test cocks
- Patented Dual-action[™] second check module
 - Poppet action at low flow
 - Swing action at high flow
- Lead Free* bronze bypass components
- CuFt or gallons bypass meter
- Silicone Elastomer
- Silicone Elastomer check discs
- Balanced chamber relief valve - No sliding seals
- AWWA C509/UL/FM resilient seated gate valves (OS&Y)
- DCDA-II single check bypass
- Flanged ends ANSI B16.1 Class 125
- Flexible groove coupling UL/FM

*The wetted surface of this product contacted by consumable water contains less than 0.25% of lead by weight.

NOTICE

The information contained herein is not intended to replace the full product installation and safety information available or the experience of a trained product installer. You are required to thoroughly read all installation instructions and product safety information before beginning the installation of this product. HORIZONTAL

Approved for Fire Protection, Waterworks, Plumbing, and Irrigation Applications.

Specifications

The Deringer 50X Reduce Pressure Detector Assembly (RPDA-II) shall utilize two independent check modules contained within a single valve housing constructed of entirely of stainless steel. Dual-action second check module shall operate as a "poppet style" check under low flow conditions, operate as a "swing style" check under high flow conditions and utilize replaceable silicone elastomer sealing discs. Valve assembly shall include two resiliently seated and inline serviceable AWWA C509 gate valves of type outside yoke and stem (OS&Y). Gate valves shall utilize a stainless steel stem with a premachined groove for installation of supervisory tamper switches. Assembly test cocks shall be handle-less and operate via a tamper resistant actuator. Assembly shall utilize a single full access service port and a cover with an "inline" replaceable elastomer seal. Relief valve shall operate without the use of sliding seals and shall be constructed entirely of stainless steel. The bypass assembly shall include a meter registering gallons or cubic feet, a single check valve and test cocks. Assembly shall be serviceable without the use of special tools.




Ames Fire & Waterworks product specifications in U.S. customary units and metric are approximate and are provided for reference only. For precise measurements, please contact Ames Fire & Waterworks Technical Service. Ames Fire & Waterworks reserves the right to change or modify product design, construction, specifications, or materials without prior notice and without incurring any obligation to make such changes and modifications on Ames Fire & Waterworks products previously or subsequently sold.

A WATTS Brand

Materials

Materials		Pressure – Temperature							
Valve Housing: Valve Cover: SOV Disks:	304 Stainless Steel 304 Stainless Steel EPDM/304SS	Temperature Range: 33°F – 140°F Working Pressure: 10 – 175psi							
SOV Shafts: Bypass Spring: RV Spring:	304 Stainless Steel 302 Stainless Steel 302 Stainless Steel	Standards AWWA C511-07 Compliant	"						
SOV Bearings: Non-wetted Bolts: Check Disks: Wetted Fasteners: Bypass Components: RV Housing:	Teflon [®] fluoropolymer/Bronze Grade 8 Zinc Plated Silicone (NSF) 18-8 Stainless Steel Lead Free Bronze 304 Stainless Steel	NSF/ANSI 372, UL CERTIFIED LEAD FREE End Connections - IPS Groove for Steel Pipe: AWWA C606 - Flange Adapters:	APPROVED						
Check Springs: Check Pins: Check Seats: O-rings: Bypass Internals: RV Hose:	17-7 Stainless Steel 17-7/18-8 Stainless Steel Noryl [®] Polymer (NSF) Buna-N (NSF) ABS Polymer (NSF) Braided Stainless Steel Wire	ANSI B16.1 Class 125							
Flow Performance		\bigcirc = Rated Flow \blacktriangle = UL Tested	○ = 15 fps						
(lpm) 7 (pisd) sso 10	57 1514 2271	3028 3785 4542 5299	6056 96 6"(X)						
<u>ا</u> 10			- 69						




* Specific orientation & agency flow characteristics available on website


Rate of Flow (gpm)

55

(kPa)

Dimensions -Weights





Size	Model	Ht		Hb L			D		Н		W		Weight		
in.		in.	mm	in.	тт	in.	тт	in.	mm	in.	тт	in.	тт	lbs	kg
6	50X	9.6	244	10.7	272	28.625	727	1.0	25	20.3	516	16.8	427	142	64



A WATTS Brand

Teflon[®] is a registered trademark of The Chemours Company. Noryl[®] is a registered trademark of SABIC Global Technologies B.V.

USA: Backflow T: (978) 689-6066 • F: (978) 975-8350 • AmesFireWater.com USA: Control Valves T: (713) 943-0688 • F: (713) 944-9445 • AmesFireWater.com Canada: T: (888) 208-8927 • F: (888) 479-2887 • AmesFireWater.ca Latin America: T: (52) 55-4122-0138 • AmesFireWater.com



© 2020 Watts